

Prisma Colour Limited

Holehouse Mill,

Marple Road,

Chisworth,

Glossop,

Derbyshire,

SK13 5DH,

UNITED KINGDOM.

t: +44 (0) 1457 856505

f: +44 (0) 1457 851055

email: info@prismacolour.com

web: www.prismacolour.com











PRISMAGUM

RUBBER COLOURING SOLUTIONS

The leading, independent European supplier

Prisma Colour Ltd is the premier supplier of colour to the rubber industry. Our customers choose Prisma Colour because of our superior technical and application knowledge enabling us to offer a perfect match.

PRISMAGUM is available in chip or slab form and also as a fully dispersed masterbatch containing no pigment agglomerates: -

PRISMAGUM-G - Chip

PRISMAGUM-S - Slab

• PRISMAGUM-X - Fully dispersed slab for printing blankets

PRISMAGUM-F - Masterbatch for FKM

We offer a fully integrated manufacturing and laboratory capability which provides the highest level of responsiveness to our customers and is focused on meeting your needs and deadlines.

PRISMAGUM Colour masterbatch for the rubber industry: -

- Based on the rubber compound of your choice, including SBR, EPR and NBR
- RAL and Pantone shades available.
- Custom colour matching
- Special effects and additive masterbatches also available
- FDA and BFR conformity is achievable if required
- EVA bound pigment dispersions
- Dry powder blends and dry liquids
- From bulk supply to sachet packs

Contact Prisma Colour now and let us offer you the perfect match.



PRISMAGUM Colour Range

This is a selection of the products we have on offer. Custom colour matches and special requirements are also available on request

| COL | O U R | | | | | |
|--------|----------|------------------|------|---------|-----------------------|-------------------------|
| | | Prisma Colours | | Active | Clariant | BASF |
| Colour | C.I. Nr. | Product | Code | Content | Product | Product |
| | _ | | | | | |
| | PR 101 | PRISMAGUM Red | C931 | 60% | n.a. | n.a. |
| | PR 38 | PRISMAGUM Red | A682 | 57% | Hostasin Red B 30 | n.a. |
| | PR 208 | PRISMAGUM Red | A683 | 55% | Hostasin Red HF2B 30 | n.a. |
| | PR 57:1 | PRISMAGUM Red | J635 | 60% | n.a. | n.a. |
| | PR 48:1 | PRISMAGUM Red | J636 | 60% | n.a. | n.a. |
| | PR 254 | PRISMAGUM Red | J752 | 50% | n.a. | Microlen Red 2030-MC |
| | PR 48:3 | PRISMAGUM Red | J996 | 50% | n.a. | n.a. |
| | PR 122 | PRISMAGUM Pink | B970 | 46% | n.a. | n.a. |
| | PO 13 | PRISMAGUM Orange | A686 | 57% | Hostasin Orange G 30 | n.a. |
| | PY 42 | PRISMAGUM Yellow | B776 | 60% | n.a. | n.a. |
| | PY 180 | PRISMAGUM Yellow | A687 | 55% | Hostasin Yellow HG | n.a. |
| | PY 83 | PRISMAGUM Yellow | A688 | 50% | Hostasin Yellow HR 30 | Microlen Yellow B3RS-MC |
| | PY 13 | PRISMAGUM Yellow | A689 | 57% | Hostasin Yellow GR 30 | n.a. |
| | PG 7 | PRISMAGUM Green | A680 | 60% | Hostasin Green GG 30 | Microlen Green GFN-MC |
| | PG 17 | PRISMAGUM Green | P318 | 60% | n.a. | n.a. |
| | PB 15:1 | PRISMAGUM Blue | J678 | 55% | Hostasin Blue A2R 30 | Microlen Blue BCS-MC |
| | PB 15:3 | PRISMAGUM Blue | J937 | 50% | n.a. | Microlen Blue 4GNP-MC |
| | Blend | PRISMAGUM Blue | P102 | 24% | n.a. | Microlen Blue A3R-MC |
| | PV 23 | PRISMAGUM Violet | P259 | 30% | n.a. | Microlen Violet B-MC |
| | Blend | PRISMAGUM Brown | A141 | 75% | n.a. | n.a. |
| | PBk 7 | PRISMAGUM Black | C644 | 50% | n.a. | Microlen Black B-MC |
| | | | | | | |

Colour representations are for illustrative purposes only and are not a true likeness.